

PRA218A DYNAMIC INSTRUMENT MICROPHONE

Description

The PRA218A is specially designed for kick drum with warm sound and high SPL capability, making it suitable for other bass band or high SPL instruments. The PRA218A is equipped with a permanent microphone clip.

Features

- Specially designed for bass drum and bass instruments.
- High SPL capacity up to 134 dB.
- Sturdy metal body.
- Durable, reliable professional performance.
- High energy neodymium magnet increases the output level.

Included



Pouch





YA2 Threaded Adapter



Specifications

Type	Dynamic
Polar Pattern	Supercardioid
Frequency Response	20 – 12,500 Hz
Sensitivity	-53 dBV/Pa (2.2 mV)
Output Impedance	500 Ω
Min. Load Impedance	500 Ω
Max. SPL	134 dB
Finish	Black
Connector	XLR3M
Dimensions	Ø43 × 120 mm (Ø1.69" × 4.72")
Net Weight	210 g (7.4 oz.)

PRA218A Frequency Response (Supercardioid)



PRA218A

EN

This information sheet contains important information for the safe use of the product. Read and follow the safety and handling instructions given here. Please keep this information sheet for future reference. If you pass on the product described overleaf, please enclose this information sheet.

Safety instructions

Intended use

This device converts acoustic signals in electrical signals. Any other use or use under the conditions excluded here is considered improper and can lead to personal injury or property damage. Neither the manufacturer nor the distributor is liable for damage resulting from improper use.

Choking hazard for children



Make sure that plastic sleeves, packaging, etc. cannot get into the reach of babies and small children. Do not allow children to use electrical devices unsupervised. They could loosen parts of the product, then swallow them and choke on them!

Place of operation

The device must not be used

- ▶ at particularly high temperatures or humidity
- ▶ in particularly dusty or polluted places
- ▶ in places where it can be exposed to moisture

General handling

To prevent damage, never use force when handling the product. Never immerse the product in liquids. Just wipe it with a clean, dry cloth. Never use liquid cleaners such as benzene, thinner, or flammable detergents to clean the product.

Disposal

Old devices



Devices with this label are subject to the current EU directive on waste electrical and electronic equipment (WEEE directive) and may not be disposed of with household waste, but only via a suitable disposal company. Ask your local authority or your specialist dealer about your options for proper disposal.

Packagings



Environmentally friendly materials have been selected for the packaging and are to be recycled. Do not just throw away plastic sleeves, packaging, etc., but recycle them. If necessary, note the instructions and labels on the packaging.